

74-30	6	2	K	T6	2	0		
BASIC SERIES	BODY MATERIAL	FINISH	OUTLET PRESSURE RANGES	SEAL MATERIAL	INLET AND OUTLET PORT TYPE AND SIZE	MAXIMUM INLET PRESSURE	GAUGE PORT OPTION	NO. OF GAUGE PORTS (SEE FIGURE)
74-30	316L SS/ST Stainless Steel (Electropolish)	10 K ₂	A - 100 mmHg absolute 15 psig 100 mmHg absolute 1.0 bar (available with 5500 psig) 0.21-2.1 bar 1.0 bar 2 - 500 psig 0.28-4.1 bar 4 - 150 psig 0.28-10.3 bar	V - Polytetrafluorethylene (PTFE) K - PTFE (available with 5500 psig) T - PTFE RW - 1/2" Female SW - 1/2" Female SZ - 1/2" Female F - 1/2" Female M - 1/2" Male S - 1/2" Male	T4 - 1/2" Tube Subs T6 - 1/2" Tube Subs T8 - 1/2" Tube Subs KA - 1/2" Male Front 40 bar (absolute only) RW - 1/2" Female SW - 1/2" Female SZ - 1/2" Female F - 1/2" Female M - 1/2" Male S - 1/2" Male	1 - 3300 psig 201 bar 2 - 1000 psig 68 bar 3 - 600 psig 41 bar 4 - 300 psig 20 bar (absolute only) 5 - 150 psig 10 bar 6 - 100 psig 6.9 bar 7 - 100 psig 6.9 bar	0 - None 1 - 1/2" H.P.C. 2 - 1/2" H.P.C. 3 - 1/2" H.P.C. 4 - 1/2" Male 5 - 1/2" Male 6 - 1/2" Male 7 - 1/2" Female 8 - 1/2" Female 9 - 1/2" Female 10 - 1/2" Female 11 - 1/2" Female 12 - 1/2" Female 13 - 1/2" Female 14 - 1/2" Female 15 - 1/2" Female 16 - 1/2" Female 17 - 1/2" Female 18 - 1/2" Female 19 - 1/2" Female 20 - 1/2" Female 21 - 1/2" Female 22 - 1/2" Female 23 - 1/2" Female 24 - 1/2" Female 25 - 1/2" Female 26 - 1/2" Female 27 - 1/2" Female 28 - 1/2" Female 29 - 1/2" Female 30 - 1/2" Female 31 - 1/2" Female 32 - 1/2" Female 33 - 1/2" Female 34 - 1/2" Female 35 - 1/2" Female 36 - 1/2" Female 37 - 1/2" Female 38 - 1/2" Female 39 - 1/2" Female 40 - 1/2" Female 41 - 1/2" Female 42 - 1/2" Female 43 - 1/2" Female 44 - 1/2" Female 45 - 1/2" Female 46 - 1/2" Female 47 - 1/2" Female 48 - 1/2" Female 49 - 1/2" Female 50 - 1/2" Female 51 - 1/2" Female 52 - 1/2" Female 53 - 1/2" Female 54 - 1/2" Female 55 - 1/2" Female 56 - 1/2" Female 57 - 1/2" Female 58 - 1/2" Female 59 - 1/2" Female 60 - 1/2" Female 61 - 1/2" Female 62 - 1/2" Female 63 - 1/2" Female 64 - 1/2" Female 65 - 1/2" Female 66 - 1/2" Female 67 - 1/2" Female 68 - 1/2" Female 69 - 1/2" Female 70 - 1/2" Female 71 - 1/2" Female 72 - 1/2" Female 73 - 1/2" Female 74 - 1/2" Female 75 - 1/2" Female 76 - 1/2" Female 77 - 1/2" Female 78 - 1/2" Female 79 - 1/2" Female 80 - 1/2" Female 81 - 1/2" Female 82 - 1/2" Female 83 - 1/2" Female 84 - 1/2" Female 85 - 1/2" Female 86 - 1/2" Female 87 - 1/2" Female 88 - 1/2" Female 89 - 1/2" Female 90 - 1/2" Female 91 - 1/2" Female 92 - 1/2" Female 93 - 1/2" Female 94 - 1/2" Female 95 - 1/2" Female 96 - 1/2" Female 97 - 1/2" Female 98 - 1/2" Female 99 - 1/2" Female 100 - 1/2" Female	

1. Per SEMTEK LMP grade






Figure A (no gauges)




Figure B (2 gauges)



Figure C (1 gauge)




Figure D (2 gauges)

